



Dimmer Cross Reference Guide



Cross-Reference Table

Leviton	Lutron	Page No.
Decora Smart®	Caséta®	4-5
Decora Digital™	Maestro®	6-7
Decora® Slide	Diva®	8-9
IllumaTech®	Skylark®	10-11
IllumaTech®	Skylark Contour®	12-13
SureSlide®	Skylark®	14
Toggle Slide	Ariadni®/Toggler®	15

Welcome to the Leviton Dimmer Cross Reference Guide

We have assembled this guide to provide you with a quick and easy cross reference of Leviton dimmers and similar Lutron models – highlighting Leviton features.

Leviton offers a wide range of dimmers in a variety of styles to meet both the functional and decorative needs of the user. Engineered to deliver exceptional performance, all Leviton dimmers are tested with leading lamps to help ensure compatibility.

Learn more at leviton.com/led

Ariadni, Caseta, Diva, Maestro, Skylark, Skylark Contour and Toggler are trademarks or registered trademarks of Lutron Electronics Co., Inc.

Decora Smart - Caseta

Decora Smart Wi-Fi® provides easy wireless lighting control with scheduling, remote control, and voice control. The complete product line includes dimmers, switches, smart plugs, fan controls, multi-button keypads, and a Voice Dimmer with Amazon Alexa Built-in.



**Leviton
Decora Smart
Dimmer**



**Lutron
Caseta Dimmer**

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen
Leviton	DW6HD	300W	600W
	DW1KD	450W	1000W
	DWVAA	300W	300W
Lutron	PD-6WCL	150W	600W

MLV Dimmers

Company	Part Number	MLV	LED/CFL	Inc/Halogen	Flr (120V)
Leviton	DW1KD	1000VA	450W	1000W	8.3A
Lutron	PD-10XND	1000VA	250W	1000W	5A
	PD-5NE	400VA	250W	500W	5A

Switches

Company	Part Number	LED/CFL	Inc/Halogen	Flr (120V)	Flr (277V)	Motor
Leviton	DW15S	600W	1800W	15A	8A	9.8FLA
Lutron	PD-5WS-DV*	5A	600W	5A	5A	3A
	PD-5ANS*	5A	600W	5A	-	3A
	PD-6ANS*	6A	720W	6A	-	3.6A

* Must de-rate if end of gang or middle of gang

Fan Speed Controls

Company	Part Number	Fan
Leviton	DW4SF	1.5A
Lutron	PD-FSQN	1.5A



Leviton Features

No Hub Required

- Less up-front expense
- No “hardware to hide”, especially for the Voice Dimmer which includes Alexa Built-in
- No proprietary repeaters necessary, uses Wi-Fi protocol

Aesthetics Matter

- Common Decora brand aesthetic matches the rest of the home and locator light makes it easy for all guests to use in the dark
- 6 Color options to match any décor
- No fin removal necessary for multi-gang installations

Additional Benefits

- Complete range of smart products including in-wall keypads, fan speed controls, receptacles and Voice Dimmer with Amazon Alexa Built-in
- Custom My Leviton app settings are easy to use to adjust on-board LEDs, fade rates, bulb type, preset level, min/max level, auto-shutoff, vacation mode, and more
- 5-Year limited warranty

Plug-In Dimmer

Company	Part Number	LED/CFL	Inc/Halogen
Leviton	DW3HL	100W	300W
Lutron	PD-3PCL-WH	100W	300W

Plug-In Outlet

Company	Part Number	LED/CFL	Inc/Halogen	Magnetic	Motor	General Use
Leviton	DW15P	600W	1500W	15A	3/4 HP	15A
Lutron	-	-	-	-	-	-

15A Receptacle

Company	Part Number	LED/CFL	Inc/Halogen	Flr (120V)	Resistive	Motor
Leviton	DW15R	600W	1500W	15A	15A	3/4 HP
Lutron	-	-	-	-	-	-

Decora Digital - Maestro

Decora Digital Dimmers feature our hallmark Decora brand aesthetic including a rocker switch paired with a contemporary slender dimmer bar for precise control of a variety of load types. Models featuring Bluetooth® technology offer a dimmer, countdown and 24-hour programmable timer in one device.



Leviton Decora Digital Dimmer



Lutron Maestro Dimmer

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen
Leviton	DDL06-BL/1L	300W	600W
Lutron	MACL-153M	150W	600W
	MA-600	-	600W
	MA-L3L3	-	300W/300W
	MA-1000	-	1000W

MLV Dimmers

Company	Part Number	MLV	LED/CFL	Inc/Halogen	Flr (120V)	Hi-Lume (120V)
Leviton	DDMX1	1000VA	450W	1000W	1000VA*	-
Lutron	MALV-600	600VA	-	-	-	-
	MALV-1000	1000VA	-	-	-	-
	MA-PRO	400VA	250W	500W	400VA	400W

* Can be used with Mark 10 and Tu-Wire

ELV Dimmers

Company	Part Number	ELV	LED/CFL	Inc/Halogen	Flr (120V)	Hi-Lume (120V)
Leviton	DDE06	600W	300W	600W	-	-
Lutron	MAELV-600	600W	-	-	-	-
	MA-PRO	500W	250W	500W	400VA	400W

Commercial Dimmers

Company	Part Number	0-10V Flr (120V)	0-10V Flr (277V)	0-10V LED (120V/277V)	Hi-Lume (120V)	Hi-Lume (277V)
Leviton	DD710	950VA	1350VA	10A	-	-
Lutron	MAF-6AM	-	-	-	6A	-
	MAF-6AM-277	-	-	-	-	6A



Leviton Features

Less Inventory/SKU

- In many instances, one SKU controls a broader range of loads
- Bluetooth devices include a dimmer, countdown and 24-hour programmable timer in one device
- Single pole or Multi-location when used with the Decora Digital coordinating or matching remotes
- All devices come packaged in white with ivory and light almond faceplates included

Easy Installation

- LED/Inc/Halogen dimmer back housing is shallow
- No fin removal necessary for multi-gang installation
- DDL06 and DDS15 utilize screw terminals

Additional Benefits

- Bluetooth control via app enables easy set up and scheduling of lights
- LED brightness display and locator light concealed in the face of the device
- 0-10V model available (no power pack required)
- 5-Year limited warranty

Switches

Company	Part Number	LED/CFL	Inc/Halogen	Flr (120V)	Flr (277V)	Resistive	Fan	Motor
Leviton	DDS15	600W	1800W	15A	6A	15A	9.8A	1/2 HP
Lutron	MA-S8AM	-	-	8A	-	-	3A	-
	MAF-S6AM-277	-	-	-	6A	-	-	-
	MA-L3S25	-	300W	-	-	2.5A	2.5A	-

Fan Speed Controls

Company	Part Number	Fan	LED/CFL	Inc/Halogen
Leviton	DDF01	1.5A	-	-
Lutron	MACL-LFQ	1.5A	75W	250W
	MA-FQ4FM	4A	-	-

Decora Slide - Diva

Decora Slide Dimmers combine a Decora brand aesthetic including a rocker switch with a slender control bar for smooth, full-range dimming.



Leviton
Decora Slide
Dimmer



Lutron
Diva
Dimmer



Leviton Features

Less Inventory/SKUs

- In many instances, one SKU controls a broad range of loads
- Single pole or 3-way when used with a standard 3-way switch
- All devices come packaged in white with ivory and light almond faceplates included

Easy Installation

- No fin removal necessary for multi-gang installations
- Terminal screws for installation on select models

Additional Benefits

- 0-10V model available (no power pack required)
- Optional locator light on device face illuminates in the dark
- 5-Year limited warranty

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen	Hi-Lume
Leviton	DSL06	300W	600W	-
Lutron	DVCL-153P	150W	600W	-
	DVCL-253P	250W	600W	350W
	DV-600P	-	600W	-
	DV-603P	-	600W	-

ELV Dimmers

Company	Part Number	ELV	LED/CFL	Inc/Halogen
Leviton	DSE06	600W	300W	-
Lutron	DVRP-253P	500W	250W	500W
	DVELV-300P	300W	-	-
	DVELV-303P	300W	-	-

Commercial Dimmers

Company	Part Number	0-10V FLR (120V)	0-10V FLR (277V)	0-10V LED (120V/277V)	Mark 10 (120V)	Mark 10 (277V)	Hi-Lume (120V)	Hi-Lume (277V)	Tu-Wire (120V)
Leviton	DS710	1200VA	1500VA	10A	-	-	-	-	-
Lutron	DVSTV	1200VA	1500VA	8A	-	-	-	-	-
	DVTV	Power pack req	Power pack req	Power pack req	-	-	-	-	-
Leviton	DSX10	-	-	-	1000VA	-	-	-	1000VA
	DSX12	-	-	-	-	1200VA	-	-	-
	DSH08	-	-	-	-	-	8A	-	-
Lutron	DVF-103P	-	-	-	-	-	8A	-	-
Leviton	DSH06	-	-	-	-	-	-	6A	-
Lutron	DVF-103P-277	-	-	-	-	-	-	6A	-
	DVFTU-5A3P	-	-	-	-	-	-	-	5A

Fan Speed Controls

Company	Part Number	Fan	LED/CFL	Inc/Halogen
Leviton	DSF01	1.5A	-	-
Lutron	DVFSQ-F	1.5A	1A	2A

MLV Dimmers

Company	Part Number	MLV	LED/CFL	Inc/Halogen
Leviton	DSM10	1000VA	450W	1000W
Lutron	DV-10P	1000VA	-	1000W
	DV-103P	1000VA	-	1000W
	DVLV-600P	600VA	-	-
	DVLV-603P	600VA	-	-

IllumaTech - Skylark

IllumaTech Slide Dimmers feature a smooth, captive slide bar for fine adjustment of lighting levels and a push button that provides preset ON/OFF switching.



Leviton
IllumaTech
Slide Dimmer



Lutron
Skylark
Dimmer



Leviton Features

Less Inventory/SKUs

- In many instances, one SKU controls a broad range of loads
- Single pole or 3-way when used with a standard 3-way switch
- All devices come packaged in white with ivory and light almond faceplates included

Additional Benefits

- Slide bar securely integrated into the design to prevent dislodging
- 0-10V model available (no power pack required)
- 5-Year limited warranty

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen
Leviton	IPL06	150W	600W
Lutron	SCL-153P	150W	600W
	S-600P (NL)	-	600W
	S-603P (NL)	-	600W
	S-603PG	-	600W
Leviton	IPI10	-	1000W
Lutron	S-10P (NL)	-	1000W
	S-103P (NL)	-	1000W

MLV Dimmers

Company	Part Number	MLV
Leviton	IPM06	600VA
	IPM10	1000VA
Lutron	SLV-600P	600VA
	SLV-603P	600VA

Commercial Dimmers

Company	Part Number	0-10V FLR (120V)	0-10V FLR (277V)	0-10V LED (120V/277V)	Mark 10 (120V)	Mark 10 (277V)	Hi-Lume (120V)	Hi-Lume (277V)	Tu-Wire
Leviton	IP710	1200VA	1500VA	10A	-	-	-	-	-
	IPX06-10	-	-	-	600VA	-	-	-	600VA
	IPX10-10	-	-	-	1000VA	-	-	-	1000VA
Lutron	SFTU5A3P	-	-	-	5A	-	-	-	5A
Leviton	IPX06-70	-	-	-	-	600VA	-	-	-
	IPX12-70	-	-	-	-	1200VA	-	-	-
Lutron	SF-10P	-	-	-	-	-	8A	-	-
	SF103P	-	-	-	-	-	8A	-	-
	SF-12P-277	-	-	-	-	-	-	6A	-
	SF-12P-277-3	-	-	-	-	-	-	6A	-

ELV Dimmers

Company	Part Number	ELV
Leviton	IPE04	400VA
Lutron	SELV-300P	300W
	SELV-303P	300W

Fan Speed Controls

Company	Part Number	Fan
Leviton	IPF01	1.5A
Lutron	SFSQ-F	1.5A
Leviton	IPF05	5A
Lutron	FSF-5E	5A

IllumaTech - Skylark Contour

IllumaTech Slide Dimmers feature a smooth, captive slide bar for fine adjustment of lighting levels and a push button that provides preset ON/OFF switching.



Leviton
IllumaTech Slide
Dimmer

Lutron
Skylark Contour
Dimmer



Leviton Features

Less Inventory/SKUs

- In many instances, one SKU controls a broad range of loads
- Single pole or 3-way when used with a standard 3-way switch
- All devices come packaged in white with ivory and light almond faceplates included

Additional Benefits

- 0-10V model available (no power pack required)
- 5-Year limited warranty

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen
Leviton	IPL06	150W	600W
Lutron	CTCL-150H	150W	600W
	CTCL-153P	150W	600W
	CT-600P	-	600W
	CT-603P	-	600W
Leviton	IPI10	-	1000W
Lutron	S-10P (NL)	-	1000W
	S-103P (NL)	-	1000W

MLV Dimmers

Company	Part Number	MLV	Inc/Halogen
Leviton	IPM06	600VA	-
	IPM10	1000VA	-
Lutron	CT-103P	600VA	1000W

ELV Dimmers

Company	Part Number	ELV	LED/CFL	Inc/Halogen
Leviton	IPE04	400VA	-	-
Lutron	CTRP-253P	500W	500W	500W
	CTELV-303P	300W	-	-

Fan Speed Controls

Company	Part Number	Fan
Leviton	IPF01	1.5A
Lutron	CTFSQ-F	1.5A

SureSlide - Skylark

SureSlide Dimmers provide smooth, slide-action, full-range dimming for a variety of load types. Preset models have separate ON/OFF switch to preserve light level.



Leviton SureSlide Dimmer

Lutron Skylark Dimmer

\$ Leviton Features

Less Inventory/SKUs

- In many instances, one SKU controls a broad range of loads
- Single pole or 3-way when used with a standard 3-way switch

Additional Benefits

- Slide bar securely integrated into the design to prevent dislodging
- Slide-to-off version that is compatible with LED/CFL loads
- Dual Fan/Light model available with dimmer compatible with LED/CFL loads
- 5-Year limited warranty

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen
Leviton	6674	150W	600W
Lutron	SCL-153P	150W	600W
	S-600P	-	600W
	S-603P	-	600W
Leviton	6672	150W	600W
Lutron	S-600	-	600W

ELV Dimmers

Company	Part Number	LED/CFL
Leviton	66EV	300VA
Lutron	SELV-300P	300W
	SELV-303P	300W

Fan Speed Controls

Company	Part Number	Fan	LED/CFL	Inc/Halogen
Leviton	661F	1.5A	-	-
Lutron	SFSQ-F	1.5A	-	-
Leviton	66DF	1.5A	150W	300W

Toggle Slide - Ariadni/Toggler

Toggle Slide Dimmers feature a traditional toggle switch that provides preset ON/OFF switching and a smooth, integrated slide bar for fine adjustment of lighting levels.



Leviton Toggle Slide Dimmer

Lutron Toggler/Ariadni Dimmer

\$ Leviton Features

Less Inventory/SKUs

- In many instances, one SKU controls a broad range of loads

Additional Benefits

- Patented hidden LED locator light built into switch
- No fin removal necessary for multi-gang installations
- 5-Year limited warranty

LED/CFL/Inc/Halogen Dimmers

Company	Part Number	LED/CFL	Inc/Halogen	MLV	Hi-Lume
Leviton	TSL06	300W	600W	-	-
Lutron	AYCL-153P	150W	600W	-	-
	AYCL-253P	250W	600W	350W	350W
	AY-600P	-	600W	-	-
	AY-603P	-	600W	-	-
Leviton	TSM10	400W	1000W	1000VA	-
Lutron	AY-10P	-	1000W	-	-
	AY-103P	-	1000W	-	-

MLV Dimmers

Company	Part Number	MLV	LED/CFL	Inc/Halogen
Leviton	TSM10	1000VA	400W	1000W
Lutron	AYLV-600P	600VA	-	-
	AYLV-603P	600VA	-	-

Commercial Dimmers

Company	Part Number	Hi-Lume
Leviton	-	-
Lutron	AYF-103P	8A
	AYF-103P-277	6A

Fan Speed Controls

Company	Part Number	Fan	Inc/Halogen
Leviton	TSF01	1.5A	-
Lutron	AYFSQ-F	1.5A	-
	AY2-LFSQ	1.5A	300W



Get it Right the First Time.

Innovative Support From The Brand You Trust

Take the guess work out of matching LED dimmers and lamps with our LED Compatibility Tool. It's the fast and easy way to ensure the dimmer you install works seamlessly with the lamp it controls.

We test leading LED lamps with our LED dimmers to identify the best pairings for improved customer satisfaction with fewer callbacks.

Learn more at leviton.com/led

LEVITON[®]

Visit leviton.com/dimmers

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747-3138

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line (8AM-10PM EST Monday-Friday): 1-800-824-3005

© 2020 Leviton Manufacturing Co., Inc. All rights reserved.

JA-053019