

In these times,  
**we are here to  
support you.**

We have increased  
our inventory to respond  
quickly to your needs.



## OEM Solutions

Leviton offers an extensive product line of commercial & industrial grade electrical, lighting and energy management devices. We are the trusted brand that provides safe, high quality products. Whether it's design assistance, delivery time, or simply products that outperform and outlast, Leviton has a complete offering of solutions for Original Equipment Manufacturers.

SAFE & RELIABLE INDUSTRIAL CONNECTIONS • OVER 115 YEARS IN THE INDUSTRY

**CONTACT YOUR APPLICATION SPECIALIST**

**LEVITON**®

## PLUGS & CONNECTORS

### Industrial Grade Plugs & Connectors

- Black & White® Extra Heavy Duty: 15-50 A, 125-600 V
- Rhino-Hide® Rough Service: 15-20 A, 125-250 V
- NEMA and Non-NEMA Configurations
- UL/Fed.Spec/CSA/NOM
- V-0-Max Locking Receptacles: 15-30 A, 125-600 V with UL V-0 flammability rating
- Industry leading limited lifetime warranty



### Wetguard® Watertight Devices

- 15-30 A, 125-600 V, Single-Phase and Three-Phase
- Straight Blade and Locking Plugs, Connectors, Receptacles & Inlets
- IEC IP66, IP67 & IP69K\*, NEMA 3, 3R, 4, 4X, 6 & 6P Enclosure Ratings

\*Plugs and connectors when mated



### IEC 60309 Pin & Sleeve Devices

- 30 A & 60 A North American Configurations
- Plugs, Connectors and Mechanical Interlocks available with Inform™ Technology
- IP66, IP67, IP68, & IP69K Rated, NSF Certified



## PORTABLE POWER

### Power Strips

- 15-20 A, 125 V
- Commercial, industrial, hospital and medical grade versions
- Medical grade versions available with load monitoring technology
- Surge protected versions



### Portable GFCIs

- 15/20 A, 125 V Cord Sets & Field-Attachable Plugs
- Auto & Manual Reset Versions
- Meets OSHA Guidelines for Personnel Protection on Job Sites



### Portable Outlet Boxes & Covers

- Single- and two-gang, feed-thru and pendant style boxes Both sides are open for full customization with a variety of cover plates
- Resistant to heat, harsh chemicals and impacts



### Rhino-Hide® Single Pole Devices

- 15 (to 150A/600V), 16/18 (to 400A/600V), and 17/22/23 (to 690A/600V) Series devices
- Insulating sleeves are color-coded for phase identification and designed for rugged applications
- Available in a range of termination styles and cord range options



### Weatherproof Covers

- For use with 15, 20, 30 and 50 A devices
- IP64 and NEMA 3R rated
- Provisions for OSHA compliant lockout/tagout
- Pre-mounted gasket and stay open feature simplify installation



Leviton is proud to help ensure adherence to the best practices in public health and safety standards. We offer a wide array of switches, wallplates, enclosures and now, a full line of LEV Series IEC 60309 Pin & Sleeve devices certified to meet NSF International hygiene requirements for food & beverage processing.

## RECEPTACLES

### Commercial and Heavy-Duty Industrial Grade Receptacles

- 15-20 A, 125-250 V
- Standard or Decora Plus™
- GFCI, Tamper-Resistant, Isolated Ground, Surge Protected, Marked "Controlled", USB and Weather-Resistant versions available



### USB Receptacles

- 15-20 A, 125-250 V
- Combined total of 5.1A charging current and 25+ watts of power
- Built-in overcurrent protection helps protect electronics from receiving too much power, which can damage the device



## SWITCHES

### Toggle and Decora Plus™ Switches

- 20 A - 120/277 V
- Pilot Light, Illuminated, Key-Locking, Momentary, Maintained, and Tamper-Resistant versions available



### Antimicrobial Treated Switches & Wallplates

- 20 A - 120/277 V
- Toggle, Decora Plus™, Conventional Wiring or Lev-Lok®
- Reduces 99.9% of bacterial growth in between normal cleanings



## LEV-LOK MODULAR DEVICES

### Lev-Lok Switches, Receptacles and Occupancy Sensors

- 3x faster installations and 5x faster swap outs than traditional wiring
- Traditional and Decora® Duplex, GFCI, Illuminated, MRI, USB, Marked Controlled Power Indication and Surge Protective Receptacles
- Single-Pole, Three-Way, Tamper-Resistant, Illuminated, and Antimicrobial Treated Switches
- Passive Infrared (PIR) and Multi-Technology (Ultrasonic and PIR) Occupancy Sensors
- Mating Lev-Lok wiring module required for use



## SURGE PROTECTIVE DEVICES

### Type 1 SPDs

- Protection for line side of electrical service equipment

### Type 2 SPDs

- Branch panel protection for single and three-phase applications

### Type 3 SPDs

- Receptacles, power strips and plug-in adapters



## SUBMETERING SOLUTIONS

### VerifEye™ Meter Kits - Indoor & Outdoor

- 100 A - 5000 A, 120 V - 277/480 V
- Single Phase & Three Phase
- Isolated Pulse Output Standard
- NEMA 1 and 4X Enclosures
- Data collection hardware and BMO 3.0 energy information software available



THE SMART CHOICE for

OEM

## LIGHTING CONTROLS

### Decora® Wall Switch Multi-Technology Occupancy Sensors

- 120-277 V AC, 50/60Hz
- LED, Incandescent/Tungsten, Fluorescent



### Ceiling-Mount Multi-Technology Occupancy Sensors

- Supports 24 V AC/DC power supplies
- Coverage Range: 500-2000 Sq. Ft.



### Multi-Technology Wall or Corner Mount Occupancy Sensors

- Supports 24 V AC/DC power supplies
- Coverage: 1200 Sq. Ft.
- Adjustable swivel neck rotates 80° vertically and 60° horizontally




### Fixture Mount PIR Sensors

- 120/277/347 V AC, 50/60Hz
- Indoor and outdoor models available



## OEM Solutions

We are here to help.



CONTACT YOUR APPLICATION SPECIALIST

Visit our Website at:

[leviton.com/oem](http://leviton.com/oem)

email: [oem@leviton.com](mailto:oem@leviton.com)

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.

Q-1247A 011724