

Fixture Mount PIR High-Bay Wet Location External Occupancy Sensor



OSFHW



OSFHW
(with Aisle Mask installed)



OSFHW with OSFOL
Adapter

Description

The Fixture Mount PIR High-Bay Wet Location External Occupancy Sensor (OSFHW) is ideal for damp or wet locations such as supermarket meat departments, food processing plants, parking garages and other wash down, high ceiling applications. The OSFHW features an IP65 rating for indoor and outdoor locations and is designed to withstand dust and pressure washers. The sensor comes with two interchangeable lenses for use in either a 360° high-bay or 360° low-bay general area and includes an aisle mask accessory.

Basic Operation

The OSFHW installs directly to an industrial fluorescent luminaire or an electrical junction box. The self-contained sensor and relay turns individual light fixtures ON or OFF based on occupancy in the detection zone. The OSFHW provides reliable coverage for up to 40 ft. mounting heights.


Installation

The OSFHW mounts directly to an industrial fluorescent fixture or an electrical junction box through a standard 1/2" knockout using the provided lock-nut. Wiring is connected inside the fixture body. Optional offset adapter is available for fixtures requiring additional clearance.

Features


- Quicksnap: built into the 1/2" nipple, this locking mechanism allows for the fastest and easiest mounting not requiring a threaded lock-nut
- Aisle mask: one unit includes interchangeable
- 360° high-bay (20-40') and 360° low-bay (8-25') lenses and an aisle mask accessory
- Fast, easy time delay setting: can be set at any time without requiring power to the sensor; time delay is variable from 30 sec-30 min
- Instantly verify fixture operation and wiring connections: "instant ON" closing relay fires lamps in under 5 seconds
- High Inrush Stability (H.I.S.) Technology:
 - Zero crossing circuitry optimizes relay operation for reliable, long-life operation
 - Robust mechanical latching relay is durable for all load types
- Auto temperature calibration: automatically adjusts the PIR sensitivity as ambient temperature rises to increase detection of heat movement through the field-of-view
- Return to last state: for safety and energy savings, the OSFHW contains a latching relay—in the event that power is lost to the device, the device will return to the last known state of the relay
- False detection intelligence: for increased energy savings and to mitigate nuisance tripping, the super-bright LED indicates advanced detection has been activated and the lights will only turn ON when true occupancy has been determined

Field of View Diagrams




*Not recommended for aisle way applications under 12' mounting height

Wiring Diagram





Mounting




FLAT LUMINAIRE

LUMINAIRE WITH LIP



Note: For taller fixtures, an offset adapter can be used for appropriate sensor positioning

Dimensions



Specifications

Electrical

Input Voltage	120-277-347VAC
Operational Frequencies	50/60 Hz
Load Rating	800VA @ 120VAC Ballast 1200VA @ 277VAC Ballast 1500VA @ 347VAC Ballast Motor: 1/4 HP Load @ 120V
Standby Power Consumption	120V - 130mW - .13W 277V - 450mW - .45W 347V - 460mW - .46W
Time Delay	30 sec-30 min (factory set to 30 sec - no power required to set)
Wire Designation	-ITW models: Line-Black, Load-Red, Neutral-White

Environmental

Operating Temperature Range	-40 to 160° F (-40 to 71° C)
Storage Temperature Range	-14 to 60° F (-25 to 71° C)
Relative Humidity	20 to 90% non-condensing

Physical

Dimensions	OSFHW: 4.75" (120.65mm)H x 3.75" (95.25mm)W
Construction	High-impact, injection molded plastic housing
Color	White

Other

Energy Codes	Can be used to comply with IECC, ASHRAE 90.1, and 2019 Title 24, Part 6 occupancy sensing requirements
Agency Listings	UL and cUL Listed, IP65 rated
Warranty	Limited 5-year

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 **tel** 800-323-8920 **tech line** (8:30AM-7:00PM ET Mon-Fri) 800-824-3005

©2021 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Ordering Information

Fixture Mount PIR High Bay Wet Location Sensor	
Cat. No.	Description
OSFHW-CTW	Fixture Mount PIR High Bay Wet Location External Occupancy Sensor, 7.5" wire lead length, interchangeable adjustable 360° low-bay (8'-20'), and high-bay (20'-40') lenses, blue aisle mask
OSFOL-00W	Watertight Offset Adapter Accessory for OSFHW, 1 position, White
OSFHL-CTW	Assembly of the OSFOL Adapter and OSFHW-CTW Sensor with 21" leads, 120-277-347VAC

Leviton Manufacturing Co., Inc. Lighting & Controls

20497 SW Teton Avenue, Tualatin, OR 97062 **tel** 800-736-6682 **tech line** (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 **tel** 800-323-8920 **tech line** (8:30AM-7:00PM ET Mon-Fri) 800-824-3005

Visit our Website at: www.leviton.com/sensors

©2021 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.